

Continuous Ink Jet

Videojet 1000 line print sample guide













Videojet 1000 line print sample guide


	Max. line speed for samples as shown (m/minute)			m/minute)	
Font/Lines	1220	1520/1550	1600 Series*	1710	70 Micron (μ) Nozzle Print Sample
4x7 Single	N/A	N/A	293	244	ABCDEFG 12345 4X7
5x5 Single	162	279	279	271	ABCDEFG 12345 5X5
5x7 Single	139	244	244	203	ABCDEFG 12345 5X7
7x9 Single	70 (70µ) 72 (60µ)	108	163	163	ABCDEFG 12345 7%9
9x12 Single	78	78	78	79	ABCDEFG 12345 9X12
10x16 Single	59	59	93	77	ABCDEFG 12345
16x24 Single	29	29	29	24	ABCDEFG 1234
25x34 Single	16	16	16	14	ABCDE 12
5x5 Twin	59	78	115	96	ABCDEFGHIJKLMNOP 1234567890 5X5TL
4x7 Twin	N/A	N/A	146	122	ABCDEFGHIJKLMNOP 1234567890 4X7TL
5x7 Twin	59	61 (70µ) 81 (60µ)	122	102	ABCDEFGHIJKLMNOP 1234567890 5X7TL
7x9 Twin	29	36 (70µ) 38 (60µ)	70	58	1254565999K-MAPE
9x12 Twin	26	26	26	21	ABCDEFGHIJKLMN 1234567890 9X12TL
10x16 Twin	16	16	16	14	ABSAFE SHIJKLMNOEPR
5x5 Three	29	36	36 (70µ) 38 (60µ)	32	ABCDEFGHIJKL 1834567890 5×5 TRI LINE
4x7 Three	N/A	N/A	81	67	ABCDEFGHIJKL 1234567890 4X7 TRI LINE
5x7 Three	27	27	67	56	ABCDEFGHIJKL 1234567890 5X7 TRI LINE
7x9 Three	16	16	16 (70μ) 37 (60μ)	31	ABCDEFGHIJKL 1234567890 7x9 TRI LINE
5x5 Four	26	26	26	21	ABCDEFGHIJKLMNO 1834567890 4 LINES OF PRINT 5XS QUAD LINE
4x7 Four	N/A	N/A	20	16	ABCDEFGHIJKLMNO 1234567890 4 LINES OF PRINT 4X7 QUAD LINE
5x7 Four	16	16	16	14	ABCDEFGHIJKLMNO 1234567890 4 LINES OF PRINT 5X7 QUAD LINE
5x5 Five	16	16	16	14	ABCDEFGHIJKLMNO 1834567890 5 LINES OF FRINT 5X5 FIVE LINE 70 MICRON NOZZLE

Videojet 1000 line print sample guide


60 Micron (μ) Nozzle Print Sample	
ABCDEFG 12345 4X7	
ABCDEFG 18345 5X5	
ABCOEFG 12345 5X7	
ABCDEFG 1234	5 7×9.
ABCDEFG 1234	15 9X12
ABCDEFG 1	
ABODEF	
ABCD	E 12
ABCDEFGHIJKLMNOF 1234567890 SXSTL	
ABCDEFGHIJKLMNOP 1234567890 4X7TL	
ABCDEFGHIJKLMNOF 1234567890 5X7TL	
ABCDEFGHIJKLM 1234567890 7>	INDP Ketl
ABCDEFGHIJK 1234567890 9X	LMN 12TL
ABODEE GHI 123456789	JKLMNOB9 O 10X16
MBCDEFOHIUKL 1834567890 SXS TRI LINE	
ABCDEFGNIUKL 1234567890 4X7 TRI LINE	
ABCDEFGHIJKL 1234567890 5X7 TRI LINE	
ABCDEFGHIJKL 1234567890 729 TRI LINE	
ABCDEFGHIJKLMNO 1834567880 4 LINES OF PRINT 5X5 GUAD LINE	
ABCOEFGHIUKLTHO 1234567890 4 LINES OF PRINT 4X7 QUAD LINE	
ABCDEFSHIJKLMNO 1234567890 4 LINES OF PRINT 5X7 QUAD LINE	
ABCDEFGHIJKLMNO 1834567890 5 LINES OF PRINT 5X5 FIVE LINE 60 MICRON NOZZLE	

LILIC *	Max. lin	e speed for samples as shown (m/minute)		
UHS *	1620/1650 UHS			
Font/Lines		50 Micron (μ) Nozzle Print Sample		
4x5 Single	508			
5x5 Single	423	MECDEFG 18848 8×8		
4x7 Single	339	ABCDEFG 12345 4X7		
5x7 Single	282	ABCDEFG 12345 5X7		
7x9 Single	254	ABCDEFG 12345 7×		
10x16 Single	121			
4x5 Twin	254	ABCDEFGHIJKLMNOP 1884567890 4X5TL		
5x5 Twin	212	ABCDEFORTUKLMNOP 1884567880 SXS TL		
4x7 Twin	191	ABCDEFGHIJKLMMOP 1234567890 4X7 TL		
5x7 Twin	158	ABCDEFGHIJKLMMOP 1234567890 5X7 TL		
7x9 Twin	91	ABCDEFGHIJKLMNDE 1234567890 7X9TL		
4x5 Three	179	PECDEFGHIJKL 1884887880 4XE TRI LIME		
5x5 Three	149			
4x7 Three	132	OBCOEFGHIJKL 1284567890 4K7 TRI LINE		
5x7 Three	110	PBCDEFGHIJK 1234567890 537 TRI LINE		
Linear print speed and character pitch are interrelated on all CIJ printers. The Videojet UHS speeds detailed in the table above are rated for 10 characters per inch. The printers maximum speed is either faster or slower based upon the chosen character pitch.				





Clear, consistent codes





The 1000 Line produces the sharpest codes in the industry. It precisely places every drop, so marks are always clear and easy to read. Dynamic Calibration automatically maintains consistent print quality, even if environmental conditions change.

The Videojet 1000 line printers are all available with the option of either a 50 micron, 60 micron or 70 micron nozzle inside the printhead. The 70 micron nozzle will benefit customers who require higher contrast or bolder characters, better visible resolution and greater throw distance. The 60 micron nozzle is well-suited for applications that require stronger character definition (ie. Asian and Arabic fonts), smaller print such as that seen on pharmaceutical and cosmetic products and additional spacing between multi-line prints. The 50 micron nozzle, and its specifically paired inks, are designed for high speed applications that require more drops per second and therefore use smaller drops. This nozzle size is also used to get smaller characters and/or more characters on the same space.

ABCDEFG

70 micron nozzle

ABCDEFG

60 micron nozzle

50 micron nozzle

Variety of ink choices to match your application

Dye based inks

Videojet offers a variety of ink colors to print on light substrates. Available in black, red, blue and green.







Dye based speciality inks

Some formulations have special characteristics like color change under retort process, optimized performance for high speeds/small nozzle size, alkali washable, food grade and visible under UV light.







Retort process

Food grade

Ultra high speed

Pigmented inks for high contrast applications

Videojet offers pigmented fluids ideal for applications requiring high contrast, bright codes on dark or difficult to mark surfaces. These inks provide easily readable codes for applications in the parts marking, extrusion, wire and cable, beverage, electronics, food and personal care markets.







 $These \ inks \ operate \ in \ the \ Videojet \ 1710 \ model \ and \ deliver \ high \ print \ quality, excellent \ adhesion \ and \ superior \ contrast.$

Videojet 1000 line print sample guide Infinite possibilities

Description	Print Sample
Four line 5x5 with 16x24 single line	BAKED FRESH DN JUNE 128 BEST IF USED \$\)
Logo with four line 5x5	85-000-00 L01 L01 1324DE 10:34:36
9x12 multi-language twin line with 10x16 single line	此期前最佳: 02/10/10 BEST IF USED BY: 02/10/10
10x16 single line over 5x7 single line	SELL BY MILLUNE 05
Three line 5x7 with 2D DataMatrix	04672203002819 R220734 13/04 - 2010
UPC-A bar code with 25x34 text	
Unlimited possibilities for mixing fonts in the same message	BAR CODE TEXT 34H
Linear bar codes Wide range of bar codes for automatic identification. UPC A&E EAN 8 & 13; Code 128 A, B&C UCC/EAN 128; Code 39; Interleaved 2 of 5	Code 39 with human readable UPC A Interleaved 2 of 5
2D DataMatrix Wide range of standard 2D and rectangular 2D DataMatrix, including GS1	
Multi-stroke To highlight words or numbers and make codes darker and bolder	5 X 7 TWIN LINE DOUBLE STROKE
Tower print* To emphasize whole message or specific characters	T Multi-stroke □ W ►□ヹЫŒ →□□ヹĦ♡ E Tower print – stacked, automatic reverse
Inverted/reversed characters Accommodates product lines going any direction and products in various orientations on the production line	RETCARAHC ESREVER 39USS3W D3LX3ANI
Unique-character languages American, Arabic, Bulgarian, Chinese, East European, European, Greek, Hebrew, Hungarian, Italian, Japanese, Japanese/Kanji, Japanese/Katakana, Korean, Russian, Simplified Chinese, Scandinavian, Thai, Traditional Chinese, Turkish, Vietnamese	合格年月日期生产保质 アカサタナハマヤラワ 有效批号班次至品使用 Katakana Chinese ートリコンション・ション・トラット Arabic
Graphics and logos Create custom logos on PC and upload via USB	TO OPEN CUT AT LINE

^{*}Only available on 1520, 1620, 1620 UHS & 1720 models

Call **800-843-3610**Email **info@videojet.com**or visit **www.videojet.com**

Videojet Technologies Inc. 1500 Mittel Blvd. Wood Dale IL 60191 / USA $@2013\ Videojet\ Technologies\ Inc. -- All\ rights\ reserved.$

Videojet Technologies Inc.'s policy is one of continued product improvement. We reserve the right to alter design and/or specifications without notice. TrueType is a registered trademark of Apple Computer, Inc.

Part No. SL000565 1000 line print sample guide- metric-0613 Printed in U.S.A.

